



# J1 PINOUT CONFIGURATION



P/N: IPD1-20-D-K (SAMTEC)

40	SIGNAL RETURN
38	+12V_AUX
36	PS_EXIST_5
34	PS_EXIST_3
32	PS_EXIST_1
30	INHIBIT_4
28	INHIBIT_2
26	SIGNAL RETURN
24	DC_OK_4
22	DC_OK_2
20	AC_FAIL_5
18	AC_FAIL_3
16	AC_FAIL_1
14	TEMP_ALARM_4
12	TEMP_ALARM_2
10	-SENSE
8	+5V/REF (*1)
6	TRIM
4	+LS
2	-LS



39	ENABLE
37	SIGNAL RETURN
35	PS_EXIST_4
33	PS_EXIST_2
31	INHIBIT_5
29	INHIBIT_3
27	INHIBIT_1
25	DC_OK_5
23	DC_OK_3
21	DC_OK_1
19	AC_FAIL_4
17	AC_FAIL_2
15	TEMP_ALARM_5
13	TEMP_ALARM_3
11	TEMP_ALARM_1
9	+5V/REF (*1)
7	NC
5	V_PROG
3	+SENSE
1	-SENSE

\*1: For HFE1600-xx/S with PMBUS option: VREF  
 For HFE1600-xx without PMBUS option: 5V