

**25W AC-DC Board Mount
KPSB25 Series**



TDK-Lambda

Points clés produit

- Répond aux normes médicales IEC/EN/UL60601-1 (3^{ème} Edition) & IEC60601-1-11
- Isolation Entrée – Sortie 4kV (2MOPP)
- Compatible ErP et US DoE rendement niveau VI
- Différents connecteurs DC disponibles en option

Specifications essentielles

- Sorties 5, 9, 12, 13.5, 15, 18, 24, 36 et 48Vdc
- Altitude 5000m
- Class II, Large plage d'entrée de 90- 240Vac
- Puissance sans charge <75mW

Applications typiques

- Equipements médicaux, cliniques et dentaires
- Equipement de surveillance
- Equipement d'imagerie
- Appareils de diagnostics

Product Highlights

- Medical approval IEC/EN/UL60601-1 (3rd Edition) & IEC60601-1-11
- Input to output isolation 4kV (2MOPP)
- ErP compliant and DoE efficiency level VI
- Custom DC output connector options

Key Specifications

- 5, 9, 12, 13.5, 15, 18, 24, 36 and 48V DC models
- Altitude 5000m
- Class II, 90 – 264VAC wide input voltage
- No load power <75mW

Typical Applications

- Hospital, dental, clinical and healthcare equipment
- Monitoring equipment
- Imaging equipment
- Diagnostic applications