



TDK-Lambda

Points clés produit

- 2 x 1" taille standard de l'industrie
- EN 50155 - Convient aux applications ferroviaires
- Plage de tension d'entrée ultra-large 18: 1
- Entrée marche/arrêt à distance
- Fonctions de protection étendues

Specifications essentielles

- Puissance : 20W
- Tension d'entrée : 8,5 - 160 Vdc
- Sortie : 5V, 12V, 15V, ±12V, ±15V ou ±24V
- Tension d'isolement E/S : 3 000 Vac
- Efficacité : jusqu'à 90 %

Applications typiques

- Équipement mobile
- Industrie
- Laboratoire, test et mesures
- télécommunications
- Traitement de données

Product Highlights

- 2 x 1" Industry standard size
- EN 50155 – Suitable for railway applications
- 18:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 20W
- Input voltage: 8.5 - 160Vdc
- Output: 5V, 12V, 15V, ±12V, ±15V or ±24V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunications
- Data processing