




The CCG-Series at a glance

	CCG1R5	CCG3	CCG6	CCG10	CCG15	CCG30
Nominal Power	1.5W	3W	6W	10W	15W	30W
						
Input	4.5-18V, 9-36V or 18-76V				9-36V or 18-76V	
Output	3.3V, 5V, 12V, 15V, $\pm 12V$ (24V) or $\pm 15V$ (30V)					
Footprint	15.7 x 10.4mm		19.0 x 12.4mm		25.4 x 25.4mm	
Height	11.5mm		11.5/11.8mm (THT/SMD)		9.9mm	
Mounting	THT or SMD				THT	
Housing	Plastic				Metal, 6-sided shielded	
Temperature Range	-40 .. +100°C		-40 .. +95°C	-40 .. +90°C	-40 .. +100°C	
Isolation	1500V _{DC}					