



TDK-Lambda

Points clés produit

- Design compact
- Répond aux normes IEC60601-1 3^{eme} Edition (2 x MoPP Isolation) & IEC60950-1
- Ventilateur à vitesse variable, <45dBA de niveau de bruit
- Garantie 7 ans

Spécifications essentielles

- Puissance de sortie 1500W jusqu'à 50°C
- EMC Courbe B en Conduit et Radié
- Sorties 12, 15, 24, 36 et 48VDC
- Sortie standby 5V 1A, Remote On/Off, DC Good, Alarme ventilation, Mise en Parallèle possible

Applications typiques

- Médical incluant les équipements pour les hôpitaux, les dentistes et tout appareils de santé
- Broadcast et Audio Professionel, Test et Mesure
- Affichages et Signalisation à LED

Product Highlights

- Enclosed Compact Construction
- IEC60601-1 3rd Edition (2 x MoPP Isolation) & IEC60950-1 Approvals
- Variable Speed Fan, <45dBA Noise Level
- 7 Year Warranty

Key Specifications

- Output Power 1500W up to 50°C
- Curve B Conducted and Radiated EMI
- Outputs 12, 15, 24, 36 and 48VDC
- 5V 1A Standby Supply, Remote On/Off, DC Good, Fan Alarm, Parallel Operation

Typical Applications

- Medical including Hospital, Dental, Clinical and Healthcare Equipment
- Broadcast and Professional Audio
- Test and Measurement
- LED Displays and Signage