



TDK-Lambda

Points clés produit

- Certifications médicales IEC/EN60601-1 (3^e Edition) & IEC/EN60601-1-2 (4^e Edition)
- Isolation entrée/sortie 4kVAC
- Faible courant de fuite (<100µA)
- Rendement DoE niveau VI et UE ErP niveau 2

Spécifications essentielles

- Puissance de 40-65W
- Entrée universelle 90-264VAC, connecteur IEC60320-C14
- Modèles 5, 12, 15, 19, 24, 28, 36 ou 48VDC
- Câble de sortie DIN 4 broches, autre version sur demande

Applications typiques

- Médical (hôpitaux, dentaire, soins)
- Monitoring
- Imagerie
- Instrumentation

Product Highlights

- Medical approval IEC/EN60601-1 (3rd Edition & IEC/EN60601-1-2 (4th Edition)
- Input to Output isolation 4kV AC
- Touch current less than 100µA
- Meets DoE level VI and EU Tier 2

Key Specifications

- 40-65W, depending on output voltage
- 90-264VAC wide input voltage, IEC60320-C14 connector
- 5, 12, 15, 19, 24, 28, 36 and 48V DC models
- Output cable 4 pin DIN, others available

Typical Applications

- Hospital, Dental, Clinical and Healthcare Equipment
- Monitoring
- Imaging
- Diagnostic applications