

AC - DC 70W Medical Adapter  
DTM70 Series



## TDK-Lambda

### Aspectos Destacados

- Certificación médica IEC/EN/UL60601-1 ED:3 para aplicaciones 2x MOPP
- Modelos con protección I (DTM70) y protección II (DTM70-C8) disponibles
- IEC/EN/UL60601-1 -11 para DTM70-C8
- Cumple con ErP con nivel de eficiencia VI del DoE

### Especificaciones Clave

- Modelos de 12, 15, 18, 24, 36 y 48V DC
- Altitud hasta 5000m
- AC 100-240V Entrada de amplio rango
- Sin pérdidas de carga <150mW
- Conector de salida con bloqueo

### Aplicaciones Típicas

- Equipos hospitalarios, dentales, clínicos y de atención sanitaria a domicilio
- Equipos de monitorización
- Equipos de diagnóstico e imagen
- Aplicaciones industriales

### Product Highlights

- Medical approval IEC/EN/UL60601-1 ED:3 for 2x MOPP applications
- Protection class I (DTM70) and Class II (DTM70-C8) models available
- IEC/EN/UL60601-1 -11 for DTM70-C8
- ErP compliant and DoE efficiency level VI

### Key Specifications

- 12, 15, 18, 24, 36 and 48V DC models
- Altitude up to 5000m
- AC 100-240V Wide-range input
- No load losses <150mW
- Locking output connector

### Typical Applications

- Hospital, dental, clinical and home healthcare equipment
- Monitoring equipment
- Imaging and diagnostic equipment
- Industrial applications