

Genesys AC – Sources
GAC 2KVA, GAC 3KVA



TDK-Lambda

Aspectos Destacados

- Potencia de salida - 2kVA o 3kVA en 1U
- LAN, USB, RS232, RS485 e interfaces analógicas aisladas de serie
- ECAT, MODBUS TCP e IEEE488 opcionales
- Factor de cresta - 4:1 de la corriente nominal

Especificaciones Clave

- Tensión de salida - 0~350Vac, 0~500Vdc
- Corriente de salida - 0~20A o 0~30A
- Frecuencia de salida: DC y 15 Hz~5 kHz
- Rango único: 0~350 Vac, 0~500 Vdc

Aplicaciones Típicas

- Productos de CA y de red
- ATE / Equipos de laboratorio (I+D)
- Automoción, movilidad eléctrica y cargadores de a bordo
- Pruebas y mediciones
- Armada y defensa

Product Highlights

- Output Power – 2kVA or 3kVA in 1U
- LAN, USB, RS232, RS485 and Isolated Analogue Interfaces as standard
- Optional ECAT, MODBUS TCP and IEEE488
- Crest Factor – 4:1 of rated current

Key Specifications

- Output Voltage – 0~350Vac, 0~500Vdc
- Output Current – 0~20A or 0~30A
- Output Frequency – DC & 15Hz~5kHz
- Single Range – 0~350Vac, 0~500Vdc

Typical Applications

- AC / Grid operated products
- ATE / Laboratory (R&D) equipment
- Automotive, e-mobility & on-board charger
- Test & Measurement
- Shipboard & Defense