



TDK-Lambda

Aspectos Destacados

- Tamaño estándar de la industria de 2 x 1"
- Blindaje de seis lados
- 4:1 Amplio rango de tensión de entrada
- Entrada de encendido/apagado remoto
- Opciones de disipadores de calor disponibles

Especificaciones Clave

- Potencia: 60W
- Tensión de entrada: 9 - 36Vdc o 18 - 75Vdc
- Tensión de aislamiento E/S 1600Vdc
- Eficiencia: hasta el 92%
- Salida: 3,3V, 5V, 12V, 15V, 24V, $\pm 12V$, $\pm 15V$ o $\pm 24V$

Aplicaciones Típicas

- Equipos móviles
- Industria
- Laboratorio, medición y pruebas
- Telecomunicaciones
- Procesamiento de datos

Product Highlights

- 2 x 1" Industry standard size
- Six sided shielding
- 4:1 Wide input voltage range
- Remote on/off input
- Fitted heat sink options available

Key Specifications

- Power: 60W
- Input voltage: 9 - 36Vdc or 18 - 75Vdc
- Isolation voltage I/O: 1600Vdc
- Efficiency: up to 92%
- Output: 3.3V, 5V, 12V, 15V, 24V, $\pm 12V$, $\pm 15V$ or $\pm 24V$

Typical Applications

- Mobile equipment
- Industry
- Laboratory, measurement and testing
- Telecommunications
- Data processing