



## TDK-Lambda

### Aspectos Destacados

- ½ Brick estándar de la industria 2.28 × 2.4
- EN 50155 - Adecuado para aplicaciones ferroviarias
- 12:1 Rango de tensión de entrada ultra amplio
- Entrada de encendido/apagado remoto
- Amplias funciones de protección

### Especificaciones Clave

- Potencia: 200W
- Tensión de entrada: 14 - 160Vdc
- Salida: 12V, 15V, 24V o 48V
- Tensión de aislamiento E/S 3000Vac
- Eficiencia: hasta el 90%

### Aplicaciones Típicas

- Ferrocarril y transporte
- Industria
- Laboratorio, medición y pruebas
- Telecomunicaciones
- Procesamiento de datos

### Product Highlights

- Half brick industry standard 2.28 × 2.4"
- EN 50155 – Suitable for railway applications
- 12:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

### Key Specifications

- Power: 200W
- Input voltage: 14 - 160Vdc
- Output: 12V, 15V, 24V or 48V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

### Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing