



TDK-Lambda

Aspectos Destacados

- ¼ Brick estándar de la industria 2,28 x 1,45"
- EN 50155 - Apto para aplicaciones ferroviarias
- 12:1 amplio Rango de tensión de entrada
- Entrada de encendido/apagado remote
- Amplias funciones de protección

Especificaciones Clave

- Potencia: 50W
- Tensión de entrada: 14 - 160Vdc
- Tensiones de Salida: 5V, 12V, 24V o 28V
- Tensión de aislamiento E/S 3000Vdc
- Eficiencia: hasta el 89%

Aplicaciones Típicas

- Ferrocarril y transporte
- Industria
- Laboratorio, medición y pruebas
- Telecomunicaciones
- Procesamiento de datos

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 12:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 50W
- Input voltage: 14 - 160Vdc
- Output: 5V, 12V, 24V or 28V
- Isolation voltage I/O: 3000Vdc
- Efficiency: up to 89%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing