



TDK-Lambda

Aspectos Destacados

- 1/4 Brick estándar de la industria 2,28 x 1,45".
- EN 50155 - Apto para aplicaciones ferroviarias
- 8:1 amplio Rango de tensión de entrada
- Entrada de encendido/apagado remoto
- Amplias funciones de protección

Especificaciones Clave

- Potencia: 75W
- Tensión de entrada: 9 - 75Vdc
- Salida: 12V, 15V, 24V, 28V o 48V
- Tensión de aislamiento E/S 3000Vac
- Eficiencia: hasta el 90%

Aplicaciones Típicas

- Ferrocarril y transporte
- Industria
- Laboratorio, medición y pruebas
- Telecomunicaciones
- Procesamiento de datos

Product Highlights

- Quarter brick industry standard 2.28 x 1.45"
- EN 50155 – Suitable for railway applications
- 8:1 Ultra-wide input voltage range
- Remote on/off input
- Extensive protection functions

Key Specifications

- Power: 75W
- Input voltage: 9 - 75Vdc
- Output: 12V, 15V, 24V, 28V or 48V
- Isolation voltage I/O: 3000Vac
- Efficiency: up to 90%

Typical Applications

- Railway and Transportation
- Industry
- Laboratory, measurement and testing
- Telecommunication
- Data processing