

AC – DC Power Supplies  
**TPS4000 4kW 3-Phase Input**



## TDK-Lambda

### Points clés produit

- Entrée triphasée 400/440/480Vac (nominal) en branchement triangle ou étoile
- Contrôle à distance du courant et de la tension
- Mise en parallèle assurée via Oring FET
- Communication PMBus™

### Specifications essentielles

- Puissance de sortie jusqu'à 4080 W
- Large plage d'ajustement des sorties 24V et 48V
- Rendement typique 92%
- Température de fonctionnement: de -40°C (démarrage) à +70°C

### Applications typiques

- Impressions numériques
- Transmission RF
- Equipements de test Semiconducteurs
- Impression 3D

### Product Highlights

- 400/440/480Vac (nominal) input 3-phase Delta or Wye
- Remote voltage and current programming
- Built in ORing FET for parallel operation
- PMBus communication

### Key Specifications

- Up to 4080W output power
- Wide range adjustable 24V and 48V outputs
- 92% typical efficiency
- -40°C (start up) to +70°C operation

### Typical Applications

- Digital printing presses
- RF transmission
- Semiconductor test equipment
- Additive manufacturing (3D printing)