



## TDK-Lambda

### Product Highlights

- High Power density
- 24 & 48Vdc Wide Range Input 4:1
- Single Output (dual output later)
- High Efficiency up to 88%
- Standard 1x1 inch Footprint
- Six sided shielding

### Key Specifications

- 3.3, 5, 12, 15Vdc Output Models
- 9-36 & 18-76Vdc input Ranges
- -40° to 85°C Operation (up to 110°C Case Temperature)
- Remote on/off, OCP (hiccup)
- +/-10% Output Adjustment Range
- 1.5kVdc Input to Output Isolation

### Typical Applications

- Industrial Control Systems
- Telecom & Datacom
- Test & Measurement
- Isolated POL
- Distributed Architectures