



TDK-Lambda

Caratteristiche del prodotto

- Approvazioni medicali IEC/EN/UL60601-1 3rd Edizione
- Isolamento ingresso – uscita 4kVAC (2MOPP)
- Corrente di dispersione a terra inferiore a 100µA
- Formato industriale standard 2 x 4 pollici

Caratteristiche principali

- Testato secondo la norma EN60601-1-2 4th Ed
- Ampio range di tensione di ingresso 90- 264VAC
- modelli 5, 12, 15, 19, 24, 28, 48V e 54VDC con modalità remote sense
- Consumo in assenza di carico <75mW

Applicazioni tipiche

- Medicali, incluse attrezzature ospedaliere, dentali, cliniche e sanitarie
- Broadcast & apparecchiature audio professionali
- Display a LED e Segnalazione

Product Highlights

- Medical approval IEC/EN/UL60601-1 3rd Edition
- Input - Output isolation 4kVAC (2MOPP)
- Earth leakage current less than 100µA
- Industry standard 2 x 4 inch foot print

Key Specifications

- Tested to EN60601-1-2 4th Edition
- 90 - 264VAC wide input voltage
- 5, 12, 15, 19, 24, 28, 48V and 54VDC models with remote sense
- No load consumption < 75mW

Typical Applications

- Medical including Hospital, Dental, Clinical and Healthcare Equipment
- Broadcast & Professional Audio
- LED Displays & Signage