



## TDK-Lambda

### Points clés produit

- 2 x 1" taille standard de l'industrie
- Blindage à six côtés
- Large plage de tension d'entrée 4:1
- Entrée marche/arrêt à distance
- Options de dissipateur de chaleur intégré disponibles

### Specifications essentielles

- Puissance : 40W
- Tension d'entrée : 9 - 36Vdc ou 18 - 75Vdc
- Tension d'isolation E/S : 1600Vdc
- Efficacité : jusqu'à 92 %
- Sortie : 3,3 V, 5 V, 12 V, 15 V, 24 V, 48 V,  $\pm 12$  V,  $\pm 15$  V ou  $\pm 24$  V

### Applications typiques

- Équipement mobile
- Industrie
- Laboratoire, test et mesures
- télécommunications
- Traitement de données

### Product Highlights

- 2 x 1" Industry standard size
- Six sided shielding
- 4:1 Wide input voltage range
- Remote on/off input
- Fitted heat sink options available

### Key Specifications

- Power: 40W
- Input voltage: 9 - 36Vdc or 18 - 75Vdc
- Isolation voltage I/O: 1600Vdc
- Efficiency: up to 92%
- Output: 3.3V, 5V, 12V, 15V, 24V, 48V,  $\pm 12$ V,  $\pm 15$ V or  $\pm 24$ V

### Typical Applications

- Mobile equipment
- Industry
- Laboratory, measurement and testing
- Telecommunications
- Data processing