

## 150W AC-DC External Power Supplies

Features	Benefits
• ErP, CEC and EISA Compliant	• Easier system compliance
• Wide Range AC Input	• Global Operation
• 87% Average Efficiency	• Consumes less energy




Specification		
Model	DT150PWxxx-C	
Input Voltage range	-	90 - 264VAC (47 - 63Hz)
Inrush Current	A	<60A at 230VAC input, 25°C ambient cold start
Input Current (Maximum)	A	2.5A
Power Factor	-	Typically 0.9 at full load (Meets EN61000-3-2)
Leakage Current	µA	<600µA at 264VAC 60Hz
Hold Up Time (Typ)	ms	>20ms at 115VAC input
Temperature Coefficient	-	±0.05%/°C
Voltage Accuracy	%	±1%
Adjustment Range	-	None
Minimum Load	A	None
Total Regulation	-	+5% / -2%
Ripple & Noise	%	See model selector
Short Circuit Protection	-	Continuous - hiccup mode (Auto Recovery)
Overvoltage Protection	V	110 - 130% of nominal (Cycle input power to reset)
Efficiency	%	>87% Avg. Active Efficiency
Operating Temperature	°C	0 to +40°C
Storage Temperature	°C	-10 to +85°C
Humidity (non condensing)	-	20 - 90% RH
Cooling	-	Convection
Withstand Voltage	-	Input to Ground 1.5kVAC, Input to Output 3kVAC for 1 min. (Output is connected to Ground internally)
Isolation Resistance	-	>20M at 25°C & 70%RH, Output to Ground 500VDC
Vibration (non operating)	-	23.52m/s <sup>2</sup> (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock	-	< 196.1 m/s <sup>2</sup> (20G)
Safety Agency Approvals	-	CSA/UL60950-1, EN609501-1, IEC60950-1
Safety Class	-	Class I
Offload Power Consumption	-	< 0.5W
Conducted & Radiated EMI	-	EN55022-B, FCC Class B
Immunity	-	EN55024
Weight (Typ)	g	780g
Size (WxLxH)	mm	85 x 170 x 44
Cable Length & Thickness	mm	1050mm; 12 to 24V Models: #14 AWG, 36 to 48V Models: #16 AWG
AC Input Connector	-	IEC 320-C14 (Accepts IEC 320-C13)
Output Connector	-	Kycon KPPx-4P or equivalent Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
MTBF	-	140,000 hours, 100% load, 25°C ambient, MIL-HNBK
Warranty	yrs	2

Notes: (1) ErP - Energy Related Products (2) Californian Energy Commission (3) EISA - Energy Independence and Security Act of 2007

## Model Selector

Model	Output (V)	Maximum Output (A)	Maximum Power (W)	Ripple & Noise (mV)	ErP2	CEC V	EISA Efficiency Level V
DT150PW120C	12	11.67	140	240	Y	Y	Y
DT150PW160C	16	9.38	150	320	Y	Y	Y
DT150PW190C	19	7.90	150	380	Y	Y	Y
DT150PW240C	24	6.25	150	480	Y	Y	Y
DT150PW360C	36	4.17	150	480	Y	Y	Y
DT150PW480C	48	3.13	150	480	Y	Y	Y

## Outline Drawing DT150-C Series



## TDK-LAMBDA EMEA

[www.emea.tdk-lambda.com](http://www.emea.tdk-lambda.com)



### TDK-Lambda France SAS

Route de Grivery  
ZAC des Delaches  
CS 41077  
91978 Courtaboeuf Cedex  
France  
Tel: +33 1 60 12 71 65  
Fax: +33 1 60 12 71 66  
[france@fr.tdk-lambda.com](mailto:france@fr.tdk-lambda.com)  
[www.fr.tdk-lambda.com](http://www.fr.tdk-lambda.com)



Italy Sales Office  
Via dei Lavoratori 128/130  
20092 Cinisello Balsamo (MI)  
Italy  
Tel: +39 02 61 29 38 63  
Fax: +39 02 61 29 09 00  
[info.italia@it.tdk-lambda.com](mailto:info.italia@it.tdk-lambda.com)  
[www.it.tdk-lambda.com](http://www.it.tdk-lambda.com)



### TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40  
77855 Achern  
Germany  
Tel: +49 7841 666 0  
Fax: +49 7841 5000  
[info.germany@de.tdk-lambda.com](mailto:info.germany@de.tdk-lambda.com)  
[www.de.tdk-lambda.com](http://www.de.tdk-lambda.com)



Austria Sales Office  
Aredstrasse 22  
2544 Leobersdorf  
Austria  
Tel: +43 2256 655 84  
Fax: +43 2256 645 12  
[info.germany@de.tdk-lambda.com](mailto:info.germany@de.tdk-lambda.com)  
[www.de.tdk-lambda.com](http://www.de.tdk-lambda.com)



### TDK-Lambda UK Ltd.

Kingsley Avenue  
Ilfracombe  
Devon EX34 8ES  
United Kingdom  
Tel: +44 (0) 12 71 85 66 66  
Fax: +44 (0) 12 71 86 48 94  
[powersolutions@uk.tdk-lambda.com](mailto:powersolutions@uk.tdk-lambda.com)  
[www.uk.tdk-lambda.com](http://www.uk.tdk-lambda.com)



### TDK-Lambda Ltd.

Kibbutz  
Givat Hashlosha 48800  
Israel  
Tel: +9 723 902 4333  
Fax: +9 723 902 4777  
[info@tdk-lambda.co.il](mailto:info@tdk-lambda.co.il)  
[www.tdk-lambda.co.il](http://www.tdk-lambda.co.il)



### Russia

Technical Support:  
St Petersburg  
Tel: +7 (812) 6580463  
Sales:  
Moscow  
Tel: +7 (499) 7557732  
[info@tdk-lambda.ru](mailto:info@tdk-lambda.ru)  
[www.tdk-lambda.ru](http://www.tdk-lambda.ru)

## Local Distribution

