

1500W AC-DC PFC Module
PF1500B series - 360V output



TDK-Lambda

Aspectos Destacados

- Apto para suministros personalizados
- Temperatura nominal de la placa base de hasta 100°C
- Refrigeración por conducción a través de la placa base
- Completamente equipado con señalización y encendido/apagado remoto

Especificaciones Clave

- 1,5kW de salida a 230Vac, 1kW a 115Vac de entrada
- Eficiencia de hasta el 96,5%.
- Formato Full Brick
- Funcionamiento en paralelo con hasta 3 unidades

Aplicaciones Típicas

- Sistemas de energía personalizados
- Arquitecturas de energía distribuida de alta tensión
- Fabricación de semiconductores
- Pruebas y mediciones

Product Highlights

- Suitable for custom supplies
- Up to 100°C rated baseplate temperature
- Conduction cooled via baseplate
- Fully featured with signalling & remote on/off

Key Specifications

- 1.5kW output at 230Vac, 1kW at 115Vac input
- Up to 96.5% efficient
- Compact full brick package
- Parallel operation with up to 3 units

Typical Applications

- Custom power systems
- High voltage distributed power architectures
- Semiconductor fabrication
- Test and measurement