



Test Report issued under
the responsibility of:



TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements

Report Reference No: E122103-A140-CB-2

Date of issue: 2015-06-26

Total number of pages: 73

CB Testing Laboratory: UL Japan, Inc.

Address: 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan

Applicant's name: TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER

Address: R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Test specification:

Standard: IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013

Test procedure: CB Scheme

Non-standard test method: N/A

Test Report Form No.: IEC60950_1F

Test Report Form originator: SGS Fimko Ltd

Master TRF: Dated 2014-02

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.



If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Switching Power Supply
Trade Mark	<i>TDK-Lambda</i>
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Model/Type reference	HWS150A-3, HWS150A-5, HWS150A-12, HWS150A-15, HWS150A-24, HWS150A-48. Maybe followed by suffix "abcde" (a is /, b is HD, c is R, d is A, B or AB, e is FG, DIN; and "abcde" may be blank)
Ratings	Input: AC100-240 V, 50-60 Hz, 1.4 A (for model HWS150A-3) and 2.0 A (for all models except for HWS150A-3)

Testing procedure and testing location:	
<input checked="" type="checkbox"/> CB Testing Laboratory Testing location / address: UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan <input type="checkbox"/> Associated CB Test Laboratory Testing location / address: Tested by (name + signature): Tetsuo Iwasaki Approved by (name + signature).....: Masatomo Takiyama	 <hr style="width: 100%;"/> 
<input type="checkbox"/> Testing Procedure: TMP/CTF Stage 1 Testing location / address: Tested by (name + signature): Approved by (name + signature).....:	<hr/> <hr/> <hr/>
<input type="checkbox"/> Testing Procedure: WMT/CTF Stage 2 Testing location / address: Tested by (name + signature): Witnessed by (name + signature) ...: Approved by (name + signature).....:	<hr/> <hr/> <hr/> <hr/>
<input type="checkbox"/> Testing Procedure: SMT/CTF Stage 3 or 4 Testing location / address: Tested by (name + signature): Approved by (name + signature).....: Supervised by (name + signature) ..:	<hr/> <hr/> <hr/> <hr/>
<input type="checkbox"/> Testing Procedure: RMT Testing location / address: Tested by (name + signature): Approved by (name + signature).....: Supervised by (name + signature) ..:	<hr/> <hr/> <hr/> <hr/>

List of Attachments	
National Differences (27 pages)	
Enclosures (44 pages)	
Summary Of Testing	
Unless otherwise indicated, all tests were conducted at UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan.	
Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	

Energy Hazard Measurements (2.1.1.5, 2.1.2, 1.2.8.10)

Capacitance Discharge (2.1.1.7)

Measurement was not conducted. Time constant was calculated.

SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4, Part 22 6.1)

Protective Bonding II (2.6.3.4, 2.6.1)

Humidity (2.9.1, 2.9.2, 5.2.2)

40±2°C, 93±2%, 120hours.

Determination of Working Voltage; Working Voltage Measurement (2.10.2)

Thin Sheet Material (2.10.5.9, 2.10.5.10, 2.10.5.6)

Transformer and Wire /Insulation Electric Strength (2.10.5.13)

Heating (4.5.1, 1.4.12, 1.4.13)

Ball Pressure (4.5.5, 4.5)

Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)

Electric Strength (5.2.2)

Component Failure (5.3.1, 5.3.4, 5.3.7)

Abnormal Operation (5.3.1 - 5.3.9)

Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)

Power Supply Output Short-Circuit/Overload (5.3.7)

ANNEX C.1-Transformer Abnormal Operation Test was considered representative of this test.

Summary of Compliance with National Differences:


Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: CA, DE, DK, EU, FI, GB, KR, SE, SI, US

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

Copy of Marking Plate

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBS that own these marks.



MODEL	A	B	C	D
HWS150A-3	3	1.4	3.3	30
HWS150A-5	5	2.0	3	30
HWS150A-12	12	2.0	1.2	3
HWS150A-15	15	2.0	1.5	0
HWS150A-24	24	2.0	24	6.5
HWS150A-48	48	2.0	48	5.3

F: COUNTRY OF MANUFACTURE WILL BE SHOWN: JAPAN, MALAYSIA OR CHINA.

Test item particulars :	
Equipment mobility	for building-in
Connection to the mains	N/A
Operating condition	continuous
Access location	N/A (for building-in)
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	+10%, -10%
Tested for IT power systems	No
IT testing, phase-phase voltage (V)	N/A
Class of equipment	Class I (earthed)
Considered current rating of protective device as part of the building installation (A)	20 A
Pollution degree (PD)	PD 2
IP protection class	IP X0
Altitude of operation (m)	Up to 4000 m
Altitude of test laboratory (m)	Approximately 10 to 20 m
Mass of equipment (kg)	approximately 0.52 kg
Possible test case verdicts:	
- test case does not apply to the test object	N / A
- test object does meet the requirement	P(Pass)
- test object does not meet the requirement	F(Fail)
Testing:	
Date(s) of receipt of test item	2013-05-14, 2013-05-16, 2013-05-23, 2013-06-06, 2013-06-27, 2013-08-09, 2013-08-21, 2013-08-22, 2013-08-30, 2013-09-09, 2014-01-30
Date(s) of Performance of tests	2013-06-11 to 2013-07-31, 2013-08-21 to 2013-09-09, 2014-01-31
General remarks:	
<p>"(see Enclosure #)" refers to additional information appended to the report. "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
Manufacturer's Declaration per Sub Clause 4.2.5 of IEC 60950-1:	
<p>The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided</p> <p>When differences exist, they shall be identified in the General Product Information section.</p>	
Name and address of Factory(ies):	WUXI TDK-LAMBDA ELECTRONICS CO LTD NO 6 XING CHUANG ER LU WUXI JIANGSU 214028 CHINA

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR
BARU JAYA GADING 26070 KUANTAN MALAYSIA

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-
1195 JAPAN

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756 JAPAN

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE
LEYU TOWN ZHANGJIAGANG 215622 JIANGSU CHINA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHI-OHASHI
TSUKUBA-SHI
IBARAKI-KEN 305-0831 JAPAN

GENERAL PRODUCT INFORMATION:

Report Summary

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

The product covered in this report is building-in type switching power supply having a single output circuit.

Output:

3.3 V (2.97V-3.96V), maximum 30 A (maximum 99W) (for HWS150A-3),
5 V (4.0V-6.0V), maximum 30 A (maximum 150W) (for HWS150A-5),
12 V (9.6V-14.4V), maximum 13 A (maximum 156W) (for HWS150A-12),
15 V (12.0V-18.0V), maximum 10 A (maximum 150W) (for HWS150A-15),
24 V (19.2V-28.8V), maximum 6.5 A (maximum 156W) (for HWS150A-24),
48 V (38.4V-52.8V), maximum 3.3 A (maximum 158.4W) (for HWS150A-48)

Model Differences

Each model is identical, except for model designation, output rating, secondary winding and internal construction of Transformer (T2), and secondary components.

Standard model is Terminal Block model without cover.

And HWS150A Series may be followed by suffix "abcde" (a is /, b is HD, c is R, d is A, B or AB, e is FG, DIN; and "abcde" may be blank)

1. HD: Model with optional Thin coating (QMJU2) on both component and solder side of PWB and maximum operating temperature is 71°C.
2. R: Model with optional ON/OFF control function.
3. A: Model with metal cover.
4. B: Model with optional input connector instead of terminal block.
5. AB: Model with metal cover and optional input connector instead of terminal block.

6. FG: Model with Low Leakage (the capacitances for Primary - FG reduced).
7. DIN: Model with DinRail Mounting Bracket.

Additional Information

This report is a re-issued report of CB Test Report Ref. No. E122103-A140-CB-1 (Amendment 2) due to following modification.

- Upgrade Standard.
- Addition of alternate component, Bobbin material of Inductor (L3), Type PM-9820.

No tests were considered necessary on the above minor modifications because of engineering judgment that the modifications do not have negatively impact to previous test results.

The Clearances and Creepage Distances have additionally been assessed for suitability up to 4000 m elevation.

UL94 Standard has requirements that meet or exceed the relevant IEC requirements.

Technical Considerations

- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: See enclosure Id. 7-01. --
- The product is intended for use on the following power systems: TN --

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- Line to Line Capacitor C1 has maximum 0.68 uF for capacitance. C1: 0.68uF was used in test. Therefore, consideration shall be given in conducting Discharge Test in the end product application with respect to the variation in C1. --
- Lines to ground Capacitors C2, C3 have maximum 2200pF for capacitance. Primary to ground Capacitor C8 has maximum 2200pF for capacitance. C2, C3 and C8: 2200pF were used in test. Therefore, consideration shall be given in conducting Touch Current Test in the end product application with respect to the variation in C2, C3 and C8. --
- Earth terminal provided on Terminal Block (TB1) or Connector (CN1) has not been evaluated as protective earthing terminal. This component is intended to be connected to a protective earth via earthed parts of end-product. If protective earthing conductor is connected to the earth terminal on Terminal Block (TB1) or Connector (CN1) in the end product, Limited Short-Circuit Test per CSA C22.2 No.04 shall be conducted. (for USA/Canada) --
- Model HWS150A-3 was tested with output Voltage Range of 2.97 - 3.96 Vdc (maximum 99 W). , Model HWS150A-5 was tested with output Voltage Range of 4.0 - 6.0 Vdc (maximum 150 W). , Model HWS150A-12 was tested with output Voltage Range of 9.6 - 14.4 Vdc (maximum 156 W). , Model HWS150A-15 was tested with output Voltage Range of 12.0 - 18.0 Vdc (maximum 150 W). , Model HWS150A-24 was tested with output Voltage Range of 19.2 - 28.8 Vdc (maximum 156 W). , Model HWS150A-48 was tested with output Voltage Range of 38.4 - 52.8 Vdc (maximum 158.4 W). , Adjustment was made via Variable Resistor (VR51). --
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: [Model HWS150A-3] Primary - Secondary: 217Vrms, 436Vpk , Primary - Ground: 202Vrms, 410Vpk , [Model HWS150A-5] Primary - Secondary: 227Vrms, 430Vpk , Primary - Ground: 217Vrms, 416Vpk , [Model HWS150A-12] Primary - Secondary: 256Vrms, 456Vpk , Primary - Ground: 234Vrms, 456Vpk ,

[Model HWS150A-15] Primary - Secondary: 254Vrms, 448Vpk , Primary - Ground: 228Vrms, 452Vpk , [Model HWS150A-24] Primary - Secondary: 258Vrms, 448Vpk , Primary - Ground: 206Vrms, 412Vpk , [Model HWS150A-48] Primary - Secondary: 257Vrms, 528Vpk , Primary - Ground: 211Vrms, 416Vpk --

- The following secondary output circuits are SELV: Output of all models --
- The following secondary output circuits are at non-hazardous energy levels: Output of all models --
- The power supply terminals and/or connectors are: Suitable for factory wiring only --
- The maximum investigated branch circuit rating is: 20 A --
- The investigated Pollution Degree is: 2 --
- Proper bonding to the end-product main protective earthing termination is: Required --
- An investigation of the protective bonding terminals has: Not been conducted --
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T2 (Class F) --
- The following end-product enclosures are required: Electrical, Fire --

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation	SI
- double insulation	DI	- reinforced insulation	RI

Indicate used abbreviations (if any)