



- Small size and lightweight
- PC Board Mountable
- -10 to +70 °C Continuous Operation
- 85 - 265VAC Wide Range Input
- World-wide Agency Approvals UL, CSA, TUV and CE Mark
- Convection Cooled
- Low Noise Conducted EMI Class B

KW Series

Compact AC-DC
PCB-Mount Power Supplies

KW Features and Benefits

Features

- Small size
- Wide input range
- No external components needed

Benefits

- Minimises PCB space
- Global use with no manual intervention
- Easy to use

Specifications

ITEMS		MODEL	5V	12V	15V	±12V	±15V
AC Input			85-265VAC 47-440Hz				
DC Input	VDC		110-340VDC				
Efficiency (typical)	%		67-74	70-77	70-77	69-75	69-75
Inrush Current Limiting	(1) A		5 & 10W: 15/30A, 15W: 20/40A				
Conducted EMI	-		FCC20780 class B, VDE0871 Class B, VCCI-2 (with external cap).				
Output Voltage Accuracy	%		± 5% (fixed)				
Line Regulation	%			0.4%			0.5%
Load Regulation	%			0.8%			5.0%
Ripple and Noise (pk-pk)	mV		120		150		
Hold-up Time (typical)	ms				17ms		
Overvoltage Protection (typical)	%				~110% (zener clamp)		
Overcurrent Protection	-				105%		
Cooling	-				Convection		
Operating Temperature	-		-10°C to 70°C, derate linearly to 25% load from 50°C to 70°C				
Humidity	%RH		30 - 90% (Operating)				
Isolation	VAC		Input to output: 3kVAC; Input to Case: 2kVAC; Output to Case: 500VAC				
Mounting	-		PC board mountable				
Safety Agency Approval	-		UL1950, CSA 22.2 No. 60950-1-03, EN60950-1 & CE Mark (LVD)				
Weight	g		5W: 75, 10W: 100, 15W: 150				
Warranty	-		1 year				

Notes: (1) 100/200VAC @ 25°C


Note KWS models are obsolete – See KWS-A series

Model Selector			
Model	Voltage (V)	Power (W)	Current (A)
Single Output			
KWS5-5	5V	5	1.00
KWS10-5	5V	10	2.00
KWS15-5	5V	15	3.00
KWS5-12	12V	5	0.45
KWS10-12	12V	10	0.90
KWS15-12	12V	15	1.30
KWS5-15	15V	5	0.35
KWS10-15	15V	10	0.70
KWS15-15	15V	15	1.00
Dual Output			
KWD5-1212	±12V	5	±0.22
KWD10-1212	±12V	10	±0.45
KWD15-1212	±12V	15	±0.65
KWD5-1515	±15V	5	±0.18
KWD10-1515	±15V	10	±0.36
KWD15-1515	±15V	15	±0.52

Pinout Table	
Pin	Function
FG	Case (Frame Ground)
AC(N)	AC Neutral
AC(L)	AC Line
-V	Negative Voltage Out
+V	Positive Voltage Out
COM	Output common

Note KWS models are obsolete – See KWS-A series

Outline Drawing KW Series



DIMENSIONS:

MODEL	A	B	C	D	E	F
KWS5	.807 (20.5)	1.77 (45.0)	.787 (20.0)	2.16 (55.0)	1.850 (47.0)	.688 (17.5)
KWS10	.807 (20.5)	1.77 (45.0)	.787 (20.0)	2.52 (64.0)	2.125 (54.0)	.688 (17.5)
KWS15	.925 (23.5)	1.889 (48.0)	.905 (23.0)	2.75 (70.0)	2.440 (62.0)	.787 (20.0)
KWD5	.807 (20.5)	1.77 (45.0)	.393 (10.0)	2.16 (55.0)	1.850 (47.0)	.688 (17.5)
KWD10	.807 (20.5)	1.77 (45.0)	.393 (10.0)	2.52 (64.0)	2.125 (54.0)	.688 (17.5)
KWD15	.925 (23.5)	1.889 (48.0)	.453 (11.5)	2.75 (70.0)	2.440 (62.0)	.787 (20.0)

WEIGHT:

MODEL	GRAMS
KWS5	75
KWS10	100
KWS15	150
KWD5	75
KWD10	100
KWD15	150

NOTE:

1. DIMENSIONS ARE IN INCHES
EXCEPT DIMENSIONS () ARE IN MM.

2. PIN: 5x .039 (1.0).



TDK-Lambda France SAS

Tel: +33 1 60 12 71 65
 tlf.fr-powersolutions@tdk.com
 www.emea.lambda.tdk.com/fr



Italy Sales Office

Tel: +39 02 61 29 38 63
 tlf.it-powersolutions@tdk.com
 www.emea.lambda.tdk.com/it



Netherlands

tlf.nl-powersolutions@tdk.com
 www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Tel: +49 7841 666 0
 tlg.powersolutions@tdk.com
 www.emea.lambda.tdk.com/de



Austria Sales Office

Tel: +43 2256 655 84
 tlg.at-powersolutions@tdk.com
 www.emea.lambda.tdk.com/at



Switzerland Sales Office

Tel: +41 44 850 53 53
 tlg.ch-powersolutions@tdk.com
 www.emea.lambda.tdk.com/ch



Nordic Sales Office

Tel: +45 8853 8086
 tlg.dk-powersolutions@tdk.com
 www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66
 tlu.powersolutions@tdk.com
 www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

Tel: +9 723 902 4333
 tli.powersolutions@tdk.com
 www.emea.lambda.tdk.com/il-en



TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324
 tla.powersolutions@tdk.com
 www.us.lambda.tdk.com



TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599
 sales.br@tdk-electronics.tdk.com
 www.tdk-electronics.tdk.com/en



TDK-Lambda Corporation

Tel: +81-3-6778-1113
 www.jp.lambda.tdk.com



TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777
 tlc.powersolutions@tdk.com
 www.lambda.tdk.com.cn



TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211
 tfs.marketing@tdk.com
 www.sg.lambda.tdk.com



TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660
 mathew.philip@tdk.com
 www.sg.lambda.tdk.com

