



■ Main Features


- High efficiency and compact size
- Overload 150%
- Constant current or hiccup mode limitation, user settable
- High operating temperature with no derating
- Low noise thermally regulated "long life" fan
- 72V output model as standard

TECHNICAL DATA

Model type	NPST961-24	NPST961-48	NPST961-72
OUTPUT DATA			
Rated voltage	24Vdc	48Vdc	72Vdc
Adj. output voltage range	23...28Vdc	45...55Vdc	72...85Vdc
Continuous current	40A	20A	13.3A
Overload limit in constant current mode	44A	22A	15A
Overload limit in hiccup mode (max. 5s)	60A	30A	20A
Load regulation	≤ 1%	≤ 0.5%	
Ripple & Noise ¹	≤ 150mVpp		
Hold up time	≥ 15ms		
Protections	<ul style="list-style-type: none"> ▪ Overload, short circuit: Constant current or Hiccup mode (user settable) ▪ Thermal protection ▪ Output overvoltage 		
Output overvoltage protection	≥ 33Vdc	≥ 68Vdc	≥ 100Vdc
Status Signals	<ul style="list-style-type: none"> ▪ DC OK - green LED ▪ OVERLOAD - red LED ▪ DC OK - dry contact (NO, 24Vdc / 1A) 		
Parallel connection ²	Possible for power or redundancy (with external ORing module)		
INPUT DATA			
Input AC rated voltage ³ Frequency	Nominal: 3 phases, 400...500Vac (UL certified) Range: 340...550Vac 47...63Hz		
Input DC rated voltage	520...725Vdc		
Input AC rated current Vin = 400Vac Vin = 500Vac	2.4A 2.1A		
Input DC rated current Vin = 520Vdc Vin = 725Vdc	2.2A 1.7A		
Inrush peak current ⁴ / I ² t	≤ 50A / 1.86A ² s		
Touch (leakage) current	≤ 0.1mA		
Internal protection fuse	None, external fuse must be provided		
Recommended external protection	Fuse 3x 10AT or 3x MCB 10A C curve It is strongly recommended to provide external surge arresters (SPD) according to local regulations.		
GENERAL DATA			
Efficiency	> 92.5%	> 92.5%	> 93%
Dissipated power	< 78W	< 78W	< 73W
Operating temperature ⁵	- 40°C...+ 70°C UL certified up to 45°C		
Derating	- 15W/°C over 45°C		
Storage temperature	- 40°C...+ 80°C		
Humidity	5...95% r.H. non condensing		
Life time expectation	63*200h (7.2 years) at 25°C ambient full load		
MTBF	<ul style="list-style-type: none"> ▪ MIL-HDBK-217F > 500'000h at 25°C ambient full load 		
Overvoltage category	<ul style="list-style-type: none"> ▪ EN50178 III 		
Pollution degree	<ul style="list-style-type: none"> ▪ IEC60664-1 2 		
Protection Class	<ul style="list-style-type: none"> ▪ CLASS I 		
Input / output isolation	4.2kVdc		
Input / ground isolation	2.2kVdc		
Output / ground isolation	0.75kVdc		
Safety Standards	<ul style="list-style-type: none"> ▪ UL508 (certified E356563) ▪ IEC/EN61010-1 ▪ IEC/EN61010-2-201 ▪ IEC/EN60950 		
EMC Emission	<ul style="list-style-type: none"> ▪ EN55011 (CISPR11) Class A ▪ EN55022 (CISPR22) Class A 		
EMC Immunity	<ul style="list-style-type: none"> ▪ EN61000-4-2 Level 3 ▪ EN61000-4-3 Level 3 ▪ EN61000-4-4 Level 3 ▪ EN61000-4-5 Level 4 ▪ EN61000-4-11 Level 2 		
Protection degree	<ul style="list-style-type: none"> ▪ EN60529 IP20 		
Vibration sinusoidal	<ul style="list-style-type: none"> ▪ IEC 60068-2-6 (5-17.8Hz: ±1.6mm; 17.8-500Hz: 2g 2hours / axis (X,Y,Z)) 		
Shock	<ul style="list-style-type: none"> ▪ IEC 60068-2-27 (30g 6ms, 20g 11ms; 3 bumps / direction, 18 bumps total) 		
Connection terminals	1.5...6mm ² , screw type header (16...10AWG) 6...16mm ² , screw type header (10...6AWG) for output on 24V model		

Case material	Aluminum
Weight	1.3kg
Size (W x H x D)	80.0 x 127.0 x 137.5mm
<p>1) Ripple and Noise are measured with 20MHz bandwidth, probe terminated with a 0.1µF MKP parallel capacitor. 2) Pay attention, set the current limitation mode jumper on C.C. mode when connecting more units in parallel. 3) In case of 2 phases operation, reduce the output load to 50% of the nominal value. 4) Peak current measured after 0.2ms from main connection; 400Vac/50Hz; Ambient temperature at 25°C; Cold Start. 5) Start-up type tested: - 40°C, possible at nominal voltage with load deration.</p> <p>Notes: - Technical parameters are typical, measured in laboratory environment at 25°C and 400Vac / 50Hz, at nominal values, after minimum 5 minutes of operation. - Power rating, losses, efficiency, ripple, thermal behaviour and start-up may change outside of the nominal rated input range. Contact factory for details. - Data may change without prior notice in order to improve the product.</p>	

DIMENSIONS



CONNECTION



Input Connection:

- 3 phases:
- L1 = phase 1
 - L2 = phase 2
 - L3 = phase 3
 - ⊕ = Earth ground
- DC:
- L1 = + Positive DC
 - L2 = - Negative DC
 - L3 = do not connect
 - ⊕ = Earth ground

Output Connection:

- + = Positive DC
 - - = Negative DC
- Signalling:
- DC OK:** dry contact
- NO
 - COM