









■ Main Features

- J High efficiency
- J 1 or 2 phases input AC 187...528Vac
- J Latched overload and short-circuit protection
- J Excellent field reliability record
-) Designed in according to EN12015, EN12016 for elevator use

WEPS160-26 - Rev. V9.0 Page 1/3



TECHNICAL DATA

TECHNICAL DATA	
Model type	WEPS160-26
OUTPUT DATA	
Rated voltage	26Vdc
Adj. output voltage range	26Vdc Fixed
Continuous current Overload limit	6A
	Up to 10A for 5s, latched protection
Short circuit peak current Load regulation	25A ≤ 1%
Ripple & Noise ¹	≤ 150mVpp
Hold up time	2 130mpp
Vin = 240Vac	≥ 20ms
Vin = 480Vac	≥ 210ms
Protections	Overload and overvoltage latched off Thermal protection Output overvoltage
Output overvoltage protection	≥ 33Vdc
Status Signals	DC OK - green LED ALARM - red LED
Parallel connection	Possible for redundancy (with external ORing module)
INPUT DATA	
	Nominal: 1/2 phases 380Vac
Input AC rated voltage	Range: 187528Vac
Frequency	4763Hz
Input AC rated current	
Vin = 187Vac	1.8A
Vin = 380Vac	1.0A
Vin = 528Vac	0.8A
Inrush peak current ² / I ² t	≤ 29A / 0.53A²s
Touch (leakage) current	≤ 0.8mA
Internal Protection fuse	None, external fuse must be provided
The state of the s	Fuse 4AT or MCB 6A C curve
Recommended external protection GENERAL DATA	It is strongly recommended to provide external surge arresters (SPD) according to local regulations.
Efficiency	> 88%
Dissipated power	< 25W
Operating temperature ³	- 40°C+ 50°C
Derating	- 15W/°C over 45°C
Storage temperature	- 40°C+ 80°C
Humidity	595% r.H. non condensing
Life time expectation	77′726h (8.8 years) at 25°C ambient full load
MTBF	 MIL-HDBK-217F > 500'000h at 25°C ambient full load
Overvoltage category Pollution degree	■ EN50178 III ■ IEC60664-1 2
Input / output isolation	4.2kVdc
Input / ground isolation	2.2kVdc
Output / ground isolation	0.75kVdc
Pac' Broand Boldfoll	■ UL508 (reference)
Safety Standards	• ULSU8 (reference) • EN60950 (reference)
	■ EN50178 (reference)
	■ EN55011 (CISPR11) Class A
EMC Emission	■ EN55022 (CISPR22) Class A
	■ EN12015 Class A
EMC Immunity	■ EN61000-4-2 Level 3
	■ EN61000-4-3 Level 3
	■ EN61000-4-4 Level 3
	■ EN61000-4-5 Level 4
	■ EN61000-4-11 Level 2
	• EN12016
Protection degree	■ EN60529 IP20
Vibration sinuosoidal	■ IEC60068-2-6 (5-17.8Hz: ±1.6mm; 17.8-500Hz: 2g 2hours / axis (X,Y,Z)
Shock	■ IEC60068-2-27 (30g 6ms, 20g 11ms; 3 bumps / direction, 18 bumps total)
Connection terminals	2.5mm², screw type header (2412AWG)
Case material	Aluminum
Weight	0.50kg
Size (W x H x D)	108.0 x 110.0 x 74.5mm
1) Ripple and Noise are measured with 20MHz had	indwidth, probe terminated with a 0.1μF MKP parallel capacitor.

- 1) Ripple and Noise are measured with 20MHz bandwidth, probe terminated with a 0.1µF MKP parallel capacitor.
- 2) Peak current measured after 0.2ms from main connection; 400Vac/50Hz; Ambient temperature at 25°C; Cold Start. 3) Start-up type tested: 40°C, possible at nominal voltage with load deration.


- For more details, performance and descriptions regarding all parameters not indicated in the above table, please refer to the instruction manual downloadable from www.nextys.com Technical parameters are typical, measured in laboratory environment at 25°C and 400Vac / 50Hz, at nominal values, after minimum 5 minutes of operation.
- Power rating, losses, efficiency, ripple, thermal behaviour and start-up may change outside of the nominal rated input range. Contact factory for details.


- Data may change without prior notice in order to improve the product.

WEPS160-26 - Rev.V9.0 Page 2/3



DIMENSIONS





CONNECTION



Input Connection:

Single phase:

- L1 = LineN = Neutral
- I = Earth ground

2 phases:

- L1 = Phase 1
- L2 = Phase 2
- I = Earth ground

Output Connection:

- + = Positive DC
- -= Negative DC

WEPS160-26 – Rev.V9.0 Page 3/3