







Test Report issued under the responsibility of:



IEC 60601-1 Medical electrical equipment Part 1: General requirements for basic safety and essential performance	
Report Reference No.	E349607-D1008-1/A0/C0-CB
Date of issue	2018-07-27
Total number of pages	120
CB Testing Laboratory	UL International Polska Sp. z o.o.
Address	Al. Krakowska 81 05-090 Sekocin Nowy Poland
Applicant's name	TDK-LAMBDA UK LTD
Address	KINGSLEY AVE ILFRACOMBE DEVON, EX34 8ES UNITED KINGDOM
Test specification:	
Standard	IEC 60601-1:1988 + A1:1991 + A2:1995
Test procedure	CB Scheme
Non-standard test method	N/A
Test Report Form No.	IEC60601_1C_II
Test Report Form Originator	Underwriters Laboratories Inc.
Master TRF	Dated 2011-11
Copyright © 2011 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved. This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context. This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.	
General disclaimer: The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB testing laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.	

Test item description:	Medical Switch Mode Power Supply	
Trade Mark:	TDK-Lambda	
Manufacturer:	Same as Applicant	
Model/Type reference:	Vega 450, Vega 650, Vega 900, Vega Lite 550 and Vega Lite 750 models (see Model Differences for details of models and nomenclature)	
Ratings:	<p>Vega 450 and Vega Lite 550. PSUs with cooling option F and without xEW and xFW options: Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 8.5 A rms max.</p> <p>All other PSUs: Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 8.5 A rms max.</p> <p>Vega 650, Vega Lite 750 and Vega 900. PSUs with cooling option F and without xEW and xFW options: Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 12 A rms max.</p> <p>All other models: Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 11 A rms max.</p> <p>(See Model Differences for details of ratings)</p>	
Testing procedure and testing location:		
<input type="checkbox"/> CB Testing Laboratory:		
Testing location/ address:		
<input type="checkbox"/> Associated CB Testing Laboratory:		
Testing location/ address:		
Tested by (name + signature):		
Approved by (name + signature):		
<input type="checkbox"/> Testing procedure: TMP:		
Testing location/ address:		
Tested by (name + signature):		
Approved by (name + signature):		
<input type="checkbox"/> Testing procedure: WMT:		
Testing location/ address:		
Tested by (name + signature):		
Witnessed by (name + signature):		

Approved by (name + signature):		
[X] Testing procedure: SMT:		
Testing location/ address:	TDK-LAMBDA UK LTD KINGSLEY AVE, ILFRACOMBE, DEVON, EX34 8ES UNITED KINGDOM	
Tested by (name + signature):	Steve Hirstwood (Tester)	
Witnessed by (name + signature):	Hima Chetty (Handler)	
Approved by (name + signature):	Krzysztof Wasilewski (Reviewer)	
Supervised by (name + signature):	Hima Chetty (Handler)	

List of Attachments (including a total number of pages in each attachment):

Refer to Appendix A of this report. All attachments are included within this report.

Summary of testing

Tests performed (name of test and test clause):

Testing location:

Refer to the Test List in Appendix B of this report if testing was performed as part of this evaluation.

Summary of compliance with National Differences

List of countries addressed: Australia, Canada, Denmark, France, Israel, Japan, Korea, Republic Of, Singapore, Slovenia, Sweden, Switzerland, USA

[X] The product fulfils the requirements of IEC 60601-1:1988 + A1:1991 + A2:1995.

Copy of marking plate

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

Refer to the enclosure(s) titled Marking Label in the Enclosures section in Appendix A of this report for a copy.

GENERAL INFORMATION	
Test item particulars:	
Classification of Installation and Use:	For building into host equipment
Device type (component/sub-assembly/ equipment/ system):	Component
Intended use (Including type of patient, application location):	To provide DC power for electronic circuits within medical equipment
Mode of operation	Continuous
Supply Connection:	Connection to mains via host equipment except for IEC60320 version
Accessories and detachable parts included:	None
Other Options Include:	None
Testing	
Date of receipt of test item(s)	2018-06-05
Dates tests performed	2018-06-06 to 2018-06-07
Possible test case verdicts:	
- test case does not apply to the test object	N/A
- test object does meet the requirement.....	Pass (P)
- test object was not evaluated for the requirement	N/E
- test object does not meet the requirement.....	Fail (F)
Abbreviations used in the report:	
- normal condition: N.C.	- single fault condition: S.F.C.
- operational insulation: OP	- basic insulation: BI
- basic insulation between parts of opposite polarity: BOP	- supplementary insulation: SI
- double insulation: DI	- reinforced insulation: RI
General remarks:	
"(see Attachment #)" refers to additional information appended to the report.	
"(see appended table)" refers to a table appended to the report.	
The tests results presented in this report relate only to the object tested.	
This report shall not be reproduced except in full without the written approval of the testing laboratory.	
List of test equipment must be kept on file and available for review.	
Additional test data and/or information provided in the attachments to this report.	
Throughout this report a point is used as the decimal separator.	
Manufacturer's Declaration per sub-clause 4.2.5 of IEC60320:2012	
The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	Yes
When differences exist; they shall be identified in the General product information section.	

Name and address of factory (ies): Same as Applicant

PANYU TRIO MICROTRONICS CO LTD
 SHIJI INDUSTRIAL ESTATE
 DONGYONG
 NANSHA
 GUANGZHOU
 GUANGDONG 511453 CHINA

GENERAL PRODUCT INFORMATION:

Report Summary

All applicable tests according to the referenced standard(s) have been carried out.
 Refer to the Report Modifications for any modifications made to this report.

Product Description

Vega 450, Vega 650, Vega 900, Vega Lite 550 and Vega Lite 750 are switch mode power supply units for building into host equipment.

Model Differences

Vega 450, Vega 650, Vega 900, Vega Lite 550 and Vega Lite 750 are switch mode power supply units for building into host equipment. There are essentially 2 converters (450 and 650) and all units use the same modules. The Vega 450 and 550 use the 450 converter whilst the Vega 650, 750 and 900 use the 650 converter.

PRODUCTS COVERED

Vega models as described below:

Units may be marked with a Product Code: Ky*, KVy* or Vy* where y may be 4, 5, 6, 7 or 9 and * may be any series of numbers from 0 to 9 and/or any letters from A to Z.

- a) V4, V5, V6, V7, V9, Vega 450, Vega 650, Vega 900, Vega Lite 550, Vega Lite 750, Vega Smart or Vega Smart Plus

Where V4 = Vega 450 range
 V5 = Vega Lite 550 range
 V6 = Vega 650 range
 V7 = Vega Lite 750 range
 V9 = Vega 900 range
 Vega Smart = Vega 450 or 650 PSU with primary digital option fitted
 Vega Smart Plus = Vega 450 or 650 PSU with primary and secondary digital options fitted

(may be prefixed by NS - # / or - where # may be up to any four letters and may be followed by -\$ where \$ may be any number between 000 to 999, indicating non-safety related model differences.

- b) Followed by: A, C, D, E, F, R, Q or P

Where F = Standard fan, forward airflow
 R = Standard fan, reverse air
 Q = Quiet fan, forward airflow
 P = Quiet fan, reverse air
 C = Customer air

A = Custom models only
 D* = Ruggedised fan, forward airflow
 E* = Ruggedised fan, reverse air

* These fans must not be used for user accessible applications.

c) Optionally followed by: F, I or S

Where F = Fast-on or quick connect input terminals
 S = Screw input terminals
 I = IEC input

d) Followed by: L, R, or T

Where L = Low Leakage
 R = Reduced Leakage
 T = Tiny Leakage

e) Optionally followed by: E, F, EV, FV, EY, FY, xEW, xFW or D

Where E = AC fail with PSU & fan enable and 5V aux supply
 F = AC fail with PSU & fan inhibit and 5V aux supply
 EV = AC fail with PSU & fan enable and 5V/300mA aux supply
 FV = AC fail with PSU & fan inhibit and 5V/300mA aux supply
 EY = AC fail with PSU & fan enable, 5V/300mA aux supply and fan fail signal
 FY = AC fail with PSU & fan inhibit, 5V/300mA aux supply and fan fail signal
 xEW = AC fail with PSU & fan enable and 5-15V/1A aux supply, where x = voltage setting
 xFW = AC fail with PSU & fan inhibit and 5-15V/1A aux supply, where x = voltage setting
 D = Primary digital option. Provides PSU inhibit and enable, fan monitor, standby supply, hours of operation, serial numbers, mains fail, over temperature warning. When secondary digital options fitted also provides status bytes, unit and module IDs, grouping, digital voltage and current limit programming, secondary inhibit and enable, secondary turn on delay, global and secondary module good, module monitoring.

Modules

B@, C@, C1Y, D@, E@, F1, F2, H@/@ or @_@, L@, W2, W5, W8 & W9.

Where the letter represents a module and @ is a number between 1 and 5, which represents the number of turns on the transformer secondary. By reference to the following table, this in turn defines the permitted voltage range of the module.

@ may optionally be followed by the letter L or H, where L and H indicate the low or high output voltage variants of the module.

For W2, W5, W8 & W9 modules only: @ is followed by F, T, E or S

where F = Fixed OVP
 T = Tracking OVP
 E = Fixed OVP, high current output
 S = Tracking OVP, high current output

Followed by F or S, where F indicates fast-on output terminals and S indicates screw output terminals.

or Z#

Where # is a number between 1 and 99. This code represents any two of the above modules that have had their outputs paralleled together. The number # is a module reference number and does not represent the number of turns. May optionally followed by F or S, where F indicates fast-on output terminals and S indicates screw output terminals.

or BB@, CC@, DD@, EE@, HH@/@ or @_@, JJ@/@ or @_@, LL@, C5B4 or B5B4

where @ is a number between 1 and 5, which represents the number of turns on the transformer secondary. For HH@/@ or @_@ the code represents one H module that has had its two outputs connected in series. For all other variants this code represents two modules, selected from those listed above, that have had their outputs connected in series. May optionally followed by F or S, where F indicates fast-on output terminals and S indicates screw output terminals.

Note: Seriated outputs may make all outputs hazardous, see Electrical & Thermal Ratings section for details. JJ@/@ or @_@ modules are HH@/@ or @_@ modules with reduced OVP and/or current ratings.

or X1, X2, X4, X8, XR1, XR2, XR4 & XR8

Where the number relates to the maximum voltage capability of the X or XR module (voltage rating is 10 multiplied by the number). The X or XR modules are connected to the output terminals of B, D, E or W modules, which may be connected in series or parallel. The X and XR modules contains diodes in series with their output (for paralleling use). The X module also has additional circuitry for remote sense, paralleling with other X modules and module inhibit. A maximum of two X or XR modules may be fitted in a PSU.

or B/S where B/S indicates that a blanking plate is fitted in place of a module.

Any of the above modules (except the X and XR modules) may have the module letter preceded with # or ## where # is represents the module output voltage.

Module Options:

N, E, P, R, T, L, K, D, V‡ or R‡

Where N = Inhibit, module good and remote sense.
 E = Enable, module good and remote sense
 P = Parallel with current share
 R = Remote sense (twin output modules only)
 T = Remote sense (one output of twin output modules only)
 L = Module good using LED indication
 K = Allows for Vega products to be paralleled with Omega products
 D = Secondary digital option (may only be fitted to single output modules). Provides Analogue voltage and resistive programming, current limit modes, inhibit output, enable output, turn on delay, module good, N+1 paralleling.
 V‡ = Voltage programmable output voltage
 R‡ = Resistance programmable output voltage

Where ‡ represents a number between 1 and 99. Each number indicates an option variant which does not affect safety, of these the following are standard variants:

1 = Inhibit, fixed current limit
 2 = Inhibit, programmable current limit
 3 = Enable, fixed current limit
 4 = Enable, programmable current limit

May additionally be marked with K4x, K5x, K6x, or V4x, V5x, V6x, V7x, V9x where x can be up to 5 digits of any letter or number between 0 and 9 indicating non-safety related model differences.

ELECTRICAL & THERMAL RATINGS:

Output modules:

Module	O/P V	Rated I	P	Slots	Turns	A/T
B1L	1 - 3.8V	20A	76W	1	1	20

B1H	2 - 5.5V	20A	110W	1	1	20
B2	3 - 9V	25A	225W	1	2	50
B3	9.1 - 16.2V	12A	195W	1	3	36
B4	16.3 - 21.5V	10A	215W	1	4	40
B5	21.6 - 31V	6A	186W	1	5	30
C1	1 - 4.1V	35A	144W	1	1	35
C1Y	1 - 4.1V	40A	164W	1	1	40
C3	9.1 - 16.2V	18A	292W	1	3	54
C4	16.3 - 21.5V	14A	301W	1	4	56
C5	21.6 - 31V	10A	310W	1	5	50
D1L	1 - 3.8V	50A	190W	1.5	1	50
D1H	3.9 - 5.5V	50A	275W	1.5	1	50
D2	3.8 - 9V	45A	405W	1.5	2	90
D3	8 - 16.5V	24A	396W	1.5	3	72
D4	14 - 21.5V	18A	387W	1.5	4	72
D5	21 - 28V	15A	420W	1.5	5	75
E1	1 - 3.8V	60A	228W	2	1	60
E2	3.8 - 8V	60A	480W	2	2	120
E3L	8 - 13.9V	40A	556W	2	3	120
E3H	14 - 15V	36A	540W	2	3	108
E4	14 - 19.9V	30A	597W	2	4	120
E5L	20 - 24V	27A	648W	2	5	135
E5H	24 - 28V	25A	650W	2	5	125
F1	1 - 3.8V	80A	640W	2	1	80
F2	3.8 - 8V	80A	640W	2	2	160
H1L/1L	1-3.8/1-3.8V	12A/8A	46W/31W	1	1/1	12/8
H1L/1H	1-3.8/3.9-5.5V	12A/8A	46W/44W	1	1/1	12/8
H1H/1L	3.9-5.5 /1-3.8V	12A/8A	66W/31W	1	1/1	12/8
H1H/1H	3.9-5.5 /3.9-5.5V	12A/8A	66W/44W	1	1/1	12/8
H1L/2	1-3.8/5-9V	12A/6A	46W/54W	1	1/2	12/12
H1H/2	3.9-5.5/5-9V	12A/6A	66W/54W	1	1/2	12/12
H1L/3	1-3.8/9.1-16.2V	12A/6A	46W/98W	1	1/3	12/18
H1H/3	3.9-5.5/9.1-16.2V	12A/6A	66W/98W	1	1/3	12/18
H1L/4	1-3.8/16.3-25V	12A/4.5A	46W/113W	1	1/4	12/18
H1H/4	3.9-5.5/16.3-25V	12A/4.5A	66W/113W	1	1/4	12/18
H2/1L	5.6-9/1-3.8V	10A/8A	90W/31W	1	2/1	20/8
H2/1H	5.6-9/3.9-5.5V	10A/8A	90W/44W	1	2/1	20/8
H2/2	5.6-9/5.6-9V	10A/6A	90W/54W	1	2/2	20/12
H2/3	5.6-9/9.1-16.2V	10A/6A	90W/98W	1	2/3	20/18
H2/4	5.6-9/16.3-25V	10A/4.5A	90W/113W	1	2/4	20/18
H3/1L	9.1-16.2/1-3.8V	10A/8A	162W/31W	1	3/1	30/8
H3/1H	9.1-16.2/3.9-5.5V	10A/8A	162W/44W	1	3/1	30/8
H3/2	9.1-16.2/5.6-9V	10A/6A	162W/54W	1	3/2	30/12
H3/3	9.1-16.2/9.1-16.2V	10A/6A	162W/98W	1	3/3	30/18
H3/4	9.1-16.2/16.3-25V	10A/4.5A	162W/113W	1	3/4	30/18
H5/1L	16.2-31/1-3.8V	5A/8A	155W/31W	1	5/1	25/8
H5/1H	16.2-31/3.9-5.5V	5A/8A	155W/44W	1	5/1	25/8

H5/2	16.2-31/5.6-9V	5A/6A	155W/54W	1	5/2	25/12
H5/3	16.2-31/9.1-16.2V	5A/6A	155W/98W	1	5/3	25/18
H5/4	16.2-31/16.3-25V	5A/4.5A	155W/113W	1	5/4	25/18
L1	4.2 - 5.5V	35A	193W	1	1	35
W2	0.25 - 7.5V	30A	225W	1	2	60
W5 (Standard)	0.25 - 32V	8.5A	272W	1	5	50
W5 (High current o/p)	0.25 - 15V 15.01 - 32V	10A 8.5A	272W	1	5	50
W8	1 - 48V	5A	240W	1	8	-
W9	1-30V	2A	60W	1	5	-
X1	10V (See Note 1)	90A	See Note 2	1	-	-
X2	20V (See Note 1)	64.5A	See Note 2	1	-	-
X4	40V (See Note 1)	32.4A	See Note 2	1	-	-
X8	80V (See Note 1)	16.2A	See Note 2	1	-	-

Note 1: Actual voltage and current output of X and XR modules is dependent, and limited by, the ratings of the modules from which it is fed. The ratings given above are additional rating limitations imposed by the X module itself.

Note 2: The maximum power output of PSUs fitted with X or XR modules is reduced from its normal rated value by the following power: $0.55 \times (\text{total X1 \& XR1 current}) + 0.7 \times (\text{total X2, X4, XR2 \& XR4 current}) + 0.9 \times (\text{total X8 \& XR8 current})$

Additional module limitations:

E2 module fitted in slots 4/5 is limited to 55A.

C1Y module can only be fitted in slot 1.

F2 module may only be fitted in slots 1/2 and is limited to 75A for ambient temperatures of greater than 45°C.

F1 module may only be fitted in slots 1/2.

For PSUs with three D modules fitted:

D1L & D1H in slots 2/3 is limited to 42A and in slots 4/5 is limited to 47A

D2 in slots 2/3 is limited to 40A

For 900W PSUs:

W2 module not permitted.

F1 and F2 modules not permitted.

PSUs fitted with a W2 module are limited to a maximum ambient of 45°C.

All the above ratings and limitations apply to the individual modules from which a series or paralleled pair is made.

SELV and Outputs Connected In Series:

Outputs are SELV except as described below:

Non-earthed outputs that have secondary's with 2 or more turns are non-SELV as a single fault in the secondary may make them exceed the SELV limit between output and earth.

Non-earthed outputs that are connected in series are non-SELV unless all the seriated outputs use 1 turn secondary's and there are no more than 3 outputs connected in series.

Outputs connected in series are non-SELV if the total output voltage + 20% of the max. rated output voltage of the output with the highest rated voltage exceeds 60Vdc (the 20% addition allows for a single fault in any one individual channel).

The total voltage of a seriated output must not exceed 160V.

If any output or seriesed output is non-SELV then all the outputs in the PSU must be considered non-SELV.

Note:

Non-SELV outputs must be guarded or a deflector fitted during installation to avoid a service engineer making inadvertent contact with the output terminals, or dropping a tool onto them.

All outputs have operational spacing's to earth, and due consideration must be given to this in the end product design.

When the IEC inlet option is fitted (option I) together with a plastic fan grill then the end face of the PSU with the fan grill may be operator accessible.

Ratings Specific to Vega 450 and Vega Lite 550 Ranges:

PSUs with cooling option F and without xEW and xFW options:

Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 8.5 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 8.5 A rms max.

Permitted orientations: Horizontal with chassis lowest, on either side or vertical with the airflow upwards.

Cooling Option	Max. Amb (°C)	Dual Width Modules Fitted	P (W)	Max. AT (Total)	Max. AT in adj	Max Modules I Rating Regions (Note 1)
F	See table below	No	See table below	180	N/A	100%
		Yes		180	180	100%
D	50	No	450	180	N/A	100%
		Yes	450	180	180	100%
R, E	50	No	450	180	N/A	100%
		Yes	450	180	162	90%
Q	50	No	450	180	N/A	100%
		Yes	450	180	180	100%
P	50	No	450	180	N/A	100%
		Yes	450	180	180	85%
C	50	See customer air cooling section for ratings				

Note 1: The PSU main transformer has three regions for module secondary's separated by two primary windings. Starting nearest slot 1, region A, primary winding, region B, primary winding, region C. The total ampere turns (AT) in any two adjacent regions is limited to that in the table above column, "Max AT in adjacent regions (note 1)". See Mains transformer regions table for modules allowed in each region. The table uses module widths with a twin output module being single width. For PSUs fitted with F2 modules "Max AT in adjacent regions" does not apply.

n/a = not applicable

Ampere Turns (AT) is the sum of (output amps x secondary turns)

Power ratings for cooling option F:

I/P V (Vrms)	O/P P (W)	Max. Amb. 40°C xEW or xFW option fitted	Max. Amb. 50°C xEW or xFW option fitted
85	425	Not permitted	425
90	470	450	450

100	520	450	500
110-149.9	570	450	550
150-264	630	450	560

Linear interpolation may be used to determine the permitted output power for input voltages between 85 and 110V.

Ratings Specific to Vega 650 and Vega 750 Lite Ranges:

PSUs with cooling option F and without xEW and xFW options:

Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 12 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 11 A rms max.

Permitted orientations: Horizontal with chassis lowest, on either side or vertical with the airflow upwards.

Cooling Option	Max. Amb (°C)	Dual Width Modules Fitted	P (W)	Max. AT (Total)	Max AT in Adj I	Max Module Rating Regions (Note 1)
F	See table below	No	See table	220	N/A	100%
		Yes	below	220	180	100%
D	50	No	650	220	N/A	100%
		Yes	650	220	180	100%
R, E	40	No	530	212	N/A	100%
		Yes	550	212	158	90%
		Yes	500	212	158	90%
		No	575	180	N/A	100%
		Yes	600	210	162	90%
		No	500	200	N/A	100%
Q	50	Yes	550	180	140	100%
		No	650	220	N/A	100%
		Yes	610	220	180	95%
		Yes	650	145	115	95%
P	40	Yes	500	203	152	85%
		Yes	420	203	152	85%
		No	500	180	N/A	100%
		Yes	450	190	162	85%
C	50	See Customer Air Cooling section for ratings				

Note 1: The PSU main transformer has three regions for module secondary's separated by two primary windings. Starting nearest slot 1, region A, primary winding, region B, primary winding, region C. The total ampere turns (AT) in any two adjacent regions is limited to that in the table above column, "Max AT in adjacent regions (note 1)". See Mains transformer regions table for modules allowed in each region. The table uses module widths with a twin output module being single width. For PSUs fitted with F2 modules "Max AT in adjacent regions" does not apply.

n/a = not applicable

Ampere Turns (AT) is the sum of (output amps x secondary turns)

Power ratings for cooling option F:

I/P V (Vrms)	O/P Power (W)	Max. Amb. 40°C xEW or xFW option fitted	Max. Amb. 50°C xEW or xFW option fitted
85	650	Not permitted	615
90	720	650	650
100	830	650	720
110-149.9	900	650	770
150-264	900	900	900

Linear interpolation may be used to determine the permitted output power for input voltages between 85 and 110V.

Ratings Specific to Vega 900 Range:

PSUs with cooling option F and without xEW and xFW options:

Input voltage: 94.5-240 V ac nom., 85-264V ac max., 47-63 Hz, 12 A rms max.

All other PSUs:

Input voltage: 100-240 V ac nom., 90-264V ac max., 47-63 Hz, 11 A rms max.

Permitted orientations: Horizontal with chassis lowest, on either side or vertical with the airflow upwards.

For input voltages equal to or greater than 150V ac ratings are as follows:

Cooling Option	Max. Amb (°C)	Dual Width Modules	P (W)	Max AT (Total)	Max AT in Adj	Max Module I Rating
F, D	50	No	900	220	180	100%
		Yes	900	220	180	100%
		No	650	220	N/A	100%
Q	50	No	750	180	N/A	100%
		Yes	750	180	140	100%
C	50	See Customer Air Cooling section for ratings				

For input voltages less than 150V ac ratings are as follows:

Cooling Option	Max. Amb (°C)	Dual Width Modules	P (W)	Max AT (Total)	Max AT in Adj	Max Module I Rating	
F	See table below	No	See table below	220	N/A	100%	
		Yes	See table below	220	180	100%	
D	50	No	650	220	N/A	100%	
		Yes	650	220	180	100%	
R, E	40	No	530	212	N/A	100%	
		Yes	550	212	158	90%	
		Yes	500	212	158	90%	
		50	No	575	180	N/A	100%
		Yes	600	210	162	90%	
Q	50	No	500	200	N/A	100%	
		Yes	550	180	140	100%	
		No	650	220	N/A	100%	
		Yes	610	220	180	95%	
		Yes	650	145	115	95%	

P	40	Yes	500	203	152	85%
	45	Yes	420	203	152	85%
	50	No	500	180	N/A	100%
		Yes	450	190	162	85%
C	50	See Customer Air Cooling section for ratings				

Power ratings for cooling option F:

I/P V (Vrms)	O/P Power (W)	Max. Amb. 40°C xEW or xFW option fitted	Max. Amb. 50°C xEW or xFW option fitted
85	650	Not permitted	615
90	720	650	650
100	830	650	720
110-149.9	900	650	770

Linear interpolation may be used to determine the permitted output power for input voltages between 85 and 110V.

Note 1: The PSU main transformer has three regions for module secondary's separated by two primary windings. Starting nearest slot 1, region A, primary winding, region B, primary winding, region C. The total ampere turns (AT) in any two adjacent regions is limited to that in the table above column, "Max AT in adjacent regions (note 1)". See Mains transformer regions table for modules allowed in each region. The table uses module widths with a twin output module being single width. For PSUs fitted with F2 modules "Max AT in adjacent regions" does not apply.

n/a = not applicable

Ampere Turns (AT) is the sum of (output amps x secondary turns)

Main transformer regions table:

SLOT 5 PRIMARY		SLOT 1 PRIMARY		SLOT 5.5 PRIMARY	
REGION C	REGION B	REGION B	REGION A	REGION B	REGION C
Slot 1 Region A	Region B	Slot 5.5. Region C	Slot 1 Region A	Region B	Slot 5.5 Region C
S	D	D	1.5	1.5	-
Blank	D	D	S	S, S	D
S	D,S	S	1.5	1.5	D
S	D	S	-	F, M, S	S, S
S	D	-	-	F, M, S	S
-	D	-	-	F, M, S	-
S	S, S, S	S	-	F, M	-
S	S, S	S	-	F, M, S	D
S	S	-	-	F, M	D
-	S	-	-	F, M, S	1.5
1.5	D	1.5	-	F, M	1.5
S	D	1.5	-	F, M 1.5	1.5
-	D	1.5	-	F, M 1.5	S
S	1.5, S	S			
S	1.5	S	Combined Modules		

S	1.5	-	S	D	D
1.5	1.5	1.5	-	D	D
S	1.5, 1.5	S	1.5	D	1.5
S	1.5	1.5	S	D	1.5
-	1.5	1.5	-	D	1.5
-	1.5	-	S	1.5, 1.5	S
-	S, S	D	S	1.5, 1.5	-
-	1.5, S	S	-	1.5, 1.5	-
1.5	1.5, S	S	1.5	1.5, D	1.5
-	D, S	S	1.5	1.5	1.5
1.5	D	S	1.5	1.5, S	S

D = Dual. S = Single, M = Module

Custom Models:

All ratings as per standard models unless otherwise stated.

Model: Vega 450 AFT B/S 24D5S 21D5S (K40054, NS-CLE-010)

Input: 85-264Vac, 47-63Hz

Maximum outputs: 24V, 12.5A; 21V, 7.143A

Orientation: All except upside down and vertical with the airflow downwards

Cooling: Papst 612NML or 612NGML or 612NMLE fan fitted with up to 66 ohms total resistance in series.

Comments: Forward air.

Model: Vega 650 BFTF B/S 24.5E5HFN

Input: 90-264Vac, 47-63Hz

Maximum output: 24.5V, 18.37A

Maximum output power: 450W

Orientation: All except upside down and vertical with the airflow downwards

Cooling: Papst 612NML or 612NGML fan fitted with up to 64 ohms total resistance in series.

Comments: Reverse air.

Model: Vega 450 AFT B/S 24E5HS (NS-CLE-011)

Input: 85-264Vac, 47-63Hz

Maximum outputs: 24V, 14.59A

Maximum output power: 350W

Orientation: All except upside down and vertical with the airflow downwards

Cooling: Papst 612NML or 612NGML fan fitted with up to 64 ohms total resistance in series.

Comments: Forward air.

Model: NS-TLC/V9QSLF 24C5SN 12Z20S (K90064*) where * may be A or B

Input: 100-240Vac nom. See table below for details

Maximum output power: See table below for details

Orientation: As standard model

OP1 V	OP1 A max	OP2 V	OP2 A max	Amb. Max.	Line V min	STBY V	STBY mA	Power W max
24	7	12	50	40	150	5	100	769
24	2.084	12	50	40	90	5	100	651
24	7	12	46.67	50	150	5	100	729
24	3.75	12	46.67	50	90	5	100	651
24	7	12	60	40	150	5	100	889
24	0	12	60	40	90	5	100	721

Model: NS-TLC/V9QSLF 24C5SN 12Z20S (K90064*) where * may be any number of letters and/or numbers except A or B, indicating non-safety related differences.

Fan: EBM-Papst 612NME

Input: 100-240Vac nom. See table below for details

Maximum output power: See table below for details

Orientation: As standard model

OP1 V	OP1 A max	OP2 V	OP2 A max	Amb. Max.	Line V min	STBY V	STBY mA	Power W max
24	7	12	50	40	150	5	100	769
24	2.084	12	50	40	90	5	100	651
24	3.75	12	46.67	40	90	5	100	651

Additional Information

Customer Air Cooling (option C):

The following method must be used for determining the safe operation of PSUs when C option (Customer Air) is fitted, i.e. fan not fitted to PSU.

For PSUs cooled by customer supplied airflow the components listed in the following table must not exceed the temperatures given. Additionally ratings specified for units with an internal fan must still be complied with, e.g. mains input voltage range, maximum output power, ampere turns, module voltage / current ratings and maximum ambient temperature. To determine the component temperatures the heating tests must be conducted in accordance with the requirements of the standards this report complies with. Consideration should also be given to the requirements of other safety standards.

Test requirements include: PSU to be fitted in its end-use equipment and operated under the most adverse conditions permitted in the end-use equipment handbook/specification and which will result in the highest temperatures in the PSU. To determine the most adverse conditions consideration should be given to the end use equipment maximum operating ambient, the PSU loading and input voltage, ventilation, end use equipment orientation, the position of doors & covers, etc. Temperatures should be monitored using type K fine wire thermocouples (secured with cyanoacrylate adhesive, or similar) placed on the hottest part of the component (out of any direct airflow) and the equipment should be run until all temperatures have stabilised.

Circuit Ref. ++	Description	Max. Temp (°C) +
-	Power transformer	130
T1, TX101, TX201	Module current transformer	127 (130)
XQ1, XT	D, E, EV, F & FV Primary Option transformers	90
XTR1	EY, FY, EV & FV Primary option transformers	90
TX1	xEW & xFW Primary option transformer	130
L1, L2, XT601	Choke winding	110 (130)
L4, T2	Choke winding	117 (130)
Various	All Choke & transformer windings	110
RLY1	Relay	100
Various	X capacitor	100
C2, C3, C14	Electrolytic Capacitors 67	105
Various	All other 10mm dia Electrolytic Capacitors	80 (105)
Various	All other 12.5mm dia Electrolytic Capacitors	85 (105)

+ The higher temperature limits in brackets may be used by product life may be reduced

++ When fitted

Marking labels are representatives of all models covered by this report.

Reissue 1

This is reissue of the CBTR Ref. No. E349607-A20-CB-1 issued 2013-03-02 with CB Certificates No. DK-25219-UL, DK-25219-A1-UL, DK-25219-A2-UL and DK-25219-A3-UL with the following changes/additions:

- added alternate fan YEN SUN TECHNOLOGY CORP type FD126025HB rated 12V, 24.5cfm.
- CBTL changed to UL International Polska

No tests conducted under this investigation due to fact that all required tests were carried out under the original investigation. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Technical Considerations

- The product was investigated to the following standards:

Main Standard(s):

IEC 60601-1:1988 + A1:1991 + A2:1995

From Country Differences:

- Australia: AS/NZS 3200-1-0
- Canada: CAN/CSA 22.2 No. 601.1-M90
- Denmark: not reported
- France: NF EN 60601-1
- Israel: SI 1011
- Japan: JIS T0601-1:1999
- Korea, Republic Of: KS C IEC 60601-1
- Singapore: SS 481 Part 1
- Slovenia: SIST EN 60601-1
- Sweden: SS-EN 60601-1:1991 + T2:1995 + A2:1996 + A1:2001
- Switzerland: SN EN 60601-1:1990 + A2:95 + A11:93 + A12:93 + A13:96
- USA: UL 60601-1

Additional Standards:

N/A

- The following additional investigations were conducted: CAN/CSA-C22.2 No. 601.1-M90 (R2005) (includes National Differences for Canada)
- UL 60601-1, 1st Edition, 2006-04-26 (includes National Differences for USA)
- EN 60601-1: 1990 + A1:1993 + A2:1995
- The product was not investigated to the following standards or clauses: Clause 52.1, Programmable Electronic Systems (IEC 601-1-4)
- Clause 48, Biocompatibility (ISO 10993-1)
- Clause 36, Electromagnetic Compatibility (IEC 601-1-2)
- The following accessories were investigated for use with the product: None
- No Other Considerations.

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 50 C

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following Production-Line tests are conducted for this product: Electric Strength, Earthing Continuity
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-Earthed Dead Metal: 350Vrms, 616Vpk, Primary-SELV: 352Vrms, 680Vpk
- The following secondary output circuits are SELV: :all, see handbook for restrictions.
- The following secondary output circuits are at hazardous energy levels: See handbook table setting for hazardous energy.
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C): Main barrier transformer OBJ3: Class F. Primary option transformer OBJ3: Class F. • For units fitted with an IEC60320-1 appliance inlet. Inlet/fan face is not allowed to be accessible for 60601-1 products

Report Modifications

Date Modified (Year-Month-Day)	Modifications Made (include Report Reference Number)	Modified By
2018-07-27	<p>This report replaces Test Report Reference No. E349607-A20-CB-2 & CB Test Certificate No. DK-70000-UL issued 2018-01-17, and all test data previously captured has been re-produced in its entirety. This following changes have been made to the report:</p> <ol style="list-style-type: none"> 1. Addition of alternate components having similar or better ratings to previous components detailed in the Critical Components Table 2. Addition of a non-standard model K90064x (where x may be any letter), employing a lower cfm rated fan 3. Deletion of the Avnet manufacturing location 4. Updated the text in the Model Differences section 6. Updated the text in the of Additional Information section <p>Only limited testing was considered necessary to make this change. Test data from E349607-D10-CB-1 which was evaluated to IEC 60601-1 Ed. 3.1 has been considered under this evaluation, as the models detailed in these reports are identical. Based on the previously conducted testing and the review of product technical documentation it has been determined that product continues to comply with the Standard and only limited testing was required.</p>	Hima Chetty